


NOTES: 1. UL LISTED AND CSA CERTIFIED AFTER HEAT SHRINKING FOR:

- A. 600 V. MAX. VOLTAGE RATING
 B. 257°F (125°C) MAX. TEMPERATURE RATING.
2. MATERIAL: A. TERMINAL- TIN PLATED COPPER WITH BRAZED SEAM.
 B. INSULATOR- HEAT SHRINKABLE POLYOLEFIN WITH HOT MELT SEALANT.
3. MINIMUM SHRINK TEMPERATURE: 300°F (150°C)
4. ALL DIMENSIONS SHOWN ARE NOMINAL.
5. INSTALLATION TOOL: CT-310
6. WIRE STRIP LENGTH: 5/16" (7.9mm)



LISTED
 (200)
 E52164



CERTIFIED
 73971

PANDUIT PART NUMBER	WIRE RANGE (AWG)	STUD SIZE S	DIMENSIONS		MAX WIRE (INSUL.) DIA	R MIN WASHER RADIUS	INSUL. COLOR	PKG QTY
			B ±.01" (.25)	W ±.005" (.13)	L (min.)			
PH18-6R	22-18	#6	.250 (6.35)	.25 (6.35)	1.05 (26.67)	.130 (3.30)	RED	25
PH18-6R	22-18	#8	.250 (6.35)	.31 (7.87)	1.08 (27.43)	.140 (3.56)	RED	25
PH18-10R	22-18	#10	.250 (6.35)	.31 (7.87)	1.08 (27.43)	.172 (4.37)	RED	25
PH18-14R	22-18	1/4"	.250 (6.35)	.47 (11.94)	1.24 (31.50)	.290 (7.37)	RED	25
PH14-6R	18-14	#6	.250 (6.35)	.31 (7.87)	1.06 (26.82)	.130 (3.30)	BLUE	25
PH14-6R	18-14	#8	.250 (6.35)	.31 (7.87)	1.03 (26.16)	.140 (3.56)	BLUE	25
PH14-10R	18-14	#10	.250 (6.35)	.32 (8.12)	1.05 (26.67)	.172 (4.37)	BLUE	25
NCPH14-10R	18-14	#10	.250 (6.35)	.32 (8.12)	1.05 (26.67)	.172 (4.37)	BLUE	500
PH14-14R	18-14	1/4"	.250 (6.35)	.46 (11.68)	1.24 (31.50)	.290 (7.37)	BLUE	25
PH14-56R	18-14	5/16"	.250 (6.35)	.46 (11.68)	1.24 (31.50)	.290 (7.37)	BLUE	25
PH14-38R	18-14	3/8"	.250 (6.35)	.53 (13.46)	1.24 (31.50)	.290 (7.37)	BLUE	25
PH10-6R	12-10	#8	.250 (6.35)	.37 (9.40)	1.22 (30.99)	.140 (3.56)	YELLOW	20
PH10-10R	12-10	#10	.250 (6.35)	.37 (9.40)	1.20 (30.48)	.172 (4.37)	YELLOW	20
NCPH10-10R	12-10	#10	.250 (6.35)	.37 (9.40)	1.20 (30.48)	.172 (4.37)	YELLOW	200
PH10-14R	12-10	1/4"	.250 (6.35)	.52 (13.21)	1.20 (30.48)	.290 (7.37)	YELLOW	20
NCPH10-14R	12-10	1/4"	.250 (6.35)	.52 (13.21)	1.20 (30.48)	.290 (7.37)	YELLOW	200
PH10-38R	12-10	3/8"	.250 (6.35)	.58 (14.99)	1.20 (30.48)	.290 (7.37)	YELLOW	20
PH10-12R	12-10	1/2"	.250 (6.35)	.72 (18.29)	1.54 (39.12)	.350 (8.89)	YELLOW	20

PANDUIT
 CORP.

FINLEY PARK, ILLINOIS

HEAT SHRINK INSULATED
 RING TERMINALS

Changed W and L dimensions for part numbers
 PH14-10R, NCPH14-10R, and L dimensions for
 part numbers PH10-14R, NCPH10-14R, PH10-38R

ADDED TOLERANCES TO B & W DIMS: REVISED L DIM OF
 PH18-14R, PH14-56R & PH14-38R PER CUSTOMER REQUEST

ADDED NCPH14-10R, NCPH10-10R, NCPH10-14R.

DESCRIPTION

CHK

REV DATE BY

ECN #

PH

CUST

ORL

SCALE

DATE

A41456

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PH14-14R-Q](#) [PH18-6R-Q](#)