


FIBER COLOR	MT-RJ POSITION	SC POSITION
ORANGE OR NATURAL	A	B
BLUE	B	A

VIEW C-C
NOT TO SCALE

MT-RJ CONNECTOR FIBER PATH

NOTES:

1. INTENDED FOR OTDR USE.
2. INSERTION LOSS: MT-RJ: 0.45dB MAX
SC: 0.50dB MAX
3. 6588080-1 CAN BE USED TO TEST MT-RJ JACKS WITH NON-SECURE HOUSINGS ONLY. 6588080-2 CAN BE USED TO TEST MT-RJ JACKS WITH ANY HOUSING.
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

NATURAL	0.61±0.05 [24.0±2.0]	100.00±1.00 [3937.00±39.00]	6588080-2
BLACK	0.61±0.05 [24.0±2.0]	100.00±1.00 [3937.00±39.00]	6588080-1
MT-RJ HOUSING COLOR	L2 METERS [INCHES]	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: KATHY HE 23JAN06	tyco Tyco Electronics Corporation Electronics Harrisburg, Pa 17105-3608	
DIMENSIONS: METERS [INCHES]		CHK: D. FENNELL 23JAN06		
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APVD: D. FENNELL 23JAN06	NAME: CABLE ASSEMBLY, FIBER OPTIC, 50/125um, OFNP, MT-RJ (NO PINS) TO SC, OTDR LAUNCH LEAD, OPTIMATE	
		PRODUCT SPEC		
		APPLICATION SPEC		
MATERIAL		WEIGHT	SIZE: A2	CAGE CODE: 00779
CUSTOMER DRAWING		DRAWING NO: C-6588080	RESTRICTED TO: -	
SCALE: NTS			SHEET: 1 OF 1	REV: A