

Nageleisen • Wrecking Bars



Nageleisen, 6-kant • Wrecking Bars, hexagon				
Art. Nr. Art. No.	-L- mm	 mm	 g	
471 400 2	400	18	770	1
471 500 2	500	18	1165	1
471 600 2	600	18	1370	1
471 700 2	700	18	1770	1
471 800 2	800	18	2175	1
472 100 2	1000	20	2700	1

Spezial-Werkzeugstahl, geschmiedet,
gehärtet, rot-pulverlackiert

Special tool steel, forged,
hardened, red powder coated



Nageleisen, rund • Wrecking Bars, round				
Art. Nr. Art. No.	-L- mm	Ø mm	 g	
474 500 2	500	20	1400	1
474 600 2	600	20	1700	1
474 700 2	700	20	2300	1
474 800 2	800	20	2600	1
474 100 2	1000	20	3200	1

Spezial-Werkzeugstahl, geschmiedet,
gehärtet, rot-pulverlackiert

Special tool steel, forged,
hardened, red powder coated



ULTIMAX-Nageleisen • ULTIMAX Wrecking Bars				
Art. Nr. Art. No.	-L- mm	 mm	 g	
475 600 2	600	26 x 16	1900	1
475 800 2	800	26 x 16	2500	1

Spezial-Werkzeugstahl
geschmiedet, gehärtet
rot-pulverlackiert

Special tool steel
forged, hardened
red powder coated