


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		C	REV ECO-06-022160	30OCT06	LH	CD



1. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. MATERIAL:
HOUSING - 94V-0 RATED POLYCARBONATE, CLEAR
TERMINAL - PHOSPHOR BRONZE, PLATED WITH 1.27 μ m [.000050] MINIMUM THICK GOLD IN LOCALIZED GOLD PLATE AREA, GOLD FLASH OVER THE REMAINDER, OVER 2.54 μ m [.000100] MINIMUM THICK NICKEL UNDERPLATE.
SHIELD - COPPER ALLOY WITH 1.27 μ m [.000050] MINIMUM SEMI-BRIGHT(SATIN) NICKEL.
LOAD BAR - PBT POLYESTER, BLACK.
3. PLUG WILL ACCEPT A 24 OR 26 AWG STRANDED CONDUCTOR, PROVIDED THE INSULATED CONDUCTOR DIAMETER IS 0.89[.035] TO 0.99[.039] WITH A SHIELDED, PLIABLE, LOOSE CABLE JACKET OF 4.83[.190] TO 5.21[.205] DIAMETER OR A SHIELDED, RIGID, HARD CABLE JACKET OF 4.83[.190] TO 5.08[.200] DIAMETER.
4. TERMINATED DIMENSION 6.15 [.242] MAXIMUM.
5. PACKAGED 500 ASSEMBLIES AND 500 LOAD BARS PER CARTON.
6. PACKAGED 100 ASSEMBLIES AND 100 LOAD BARS PER BOX.
7. PACKAGED 25 ASSEMBLIES AND 25 LOAD BARS PER BAG.
8. UL LISTED: FILE NUMBER E81956.

7	5-569552-4
6	5-569552-3
5	5-569552-2
PACKAGED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 10-12-95	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK C. WHITT 10-31-95		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. LAURER 11-7-95	NAME MODULAR PLUG ASSEMBLY, 8 POSITION,SHIELDED,ROUND CABLE, STRANDED WIRE,HIGH PERFORMANCE	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC 108-1163 APPLICATION SPEC 114-6053		
MATERIAL		WEIGHT -	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 1
			REV C	