




PRODUCT NUMBER	MATING LENGTH		TAIL LENGTH		BEND DIM		PIN TO SIDE		BODY WIDTH		POLARIZED POSITION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	DIM J	DIM J	DIM K	DIM K	
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	
79278-XY	0.230	5.84	0.120	3.05	0.060	1.52	0.045	1.14	0.190	4.83	A-2
79288-XY	0.230	5.84	0.120	3.05	0.060	1.52	0.070	1.78	0.240	6.10	A-2
79289-XY	0.318	8.08	0.120	3.05	0.060	1.52	0.070	1.78	0.240	6.10	A-2
87294-XY	0.318	8.08	0.120	3.05	0.060	1.52	0.070	1.78	0.240	6.10	B-4

NOTE:

- FOR PRODUCT GEOMETRY AND GENERAL INFORMATION SEE DRAWING 93198.
- ANY NUMBER OF POSITIONS FROM 4 (2X2) THRU 72 (2X36).
XXXXX-YYYH
HIGH TEMPERATURE PLASTIC
NO. OF POSITIONS
PIN PLATING
BASE PART NUMBER
- PACKAGED IN POLY BAGS ONLY.
- PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON POST OR TAIL, OPTIONALLY (78~295u"/2~7.5u") TIN ON TAIL.
- "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."



PIN PLATING CODES:

XXXXX-1YY	30u"/0.76u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni
XXXXX-2YY	15u"/0.38u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni
XXXXX-3YY	50u"/1.27u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni
XXXXX-4YY	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 5)
XXXXX-4YYHLF	
XXXXX-5YY	15u"/0.38u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni
XXXXX-6YY	30u"/0.76u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni
XXXXX-7YY	30u"/0.76u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni
XXXXX-8YY	15u"/0.38u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni
XXXXX-9YY	15u"/0.38u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni
XXXXX-0YY	30u"/0.76u MIN (SEE NOTE 4) OVER 50u"/1.27u MIN Ni

rev	ecn no	dr	date
E	V30713	DEW	4/16/93
F	V41575	HTB	10/25/94
G	V20832	GIP	7/11/02
H	V21830	HTB	2/14/03
J	M06-0269	AEA	7/19/06
K	N11-0118	J.Z	2011-04-14
L	ELX-N-16105	ZK	2013-10-22

www.fciconnect.com			surface 6.4 ISO 1302	tolerance std ISO 406 ISO 1101	projection A4	INCH/MM Scale 1.000
Dr	T. BREWBAKER	10/25/94	TOLERANCES UNLESS OTHERWISE SPECIFIED		size	ECN
Eng	T. HANNA	10/25/94	ANGULAR	LINEAR	0.X ±0.3	0.XX ±0.15
Chr	T. HANNA	10/25/94	0° ±2°		0.XXX ±0.05	
Appr	T. HANNA	10/25/94	Product family BERGSTIK		Spec ref	
FCI			title BERGSTIK® II HEADER .100 D/R R/A POL.		dwg no 79278	Rev. L
catalog no			CUSTOMER		sheet 1 of 1	