




© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

P	F	ZONE	LTR	REVISIONS		
				DESCRIPTION	DATE	APPROVED
			01	ADDED 1--1 6499 m.s.	2-20-80	WAP
			02	REVISED 6924 m.s.	10-80	WAP
			A	REVISED FINISH 7226 m.s.	2-81	WAP
			A1	ECN 7979 & 7982 wpl	6-82	EAM
			B	REV PER ECNAB0522 db	2-85	EAM
			C	REV PER ECN AB-1454 db	3-86	EAM
			D	REV PER DF-0117 TS	8/88	WAP
			E	REV PER DF-6974 TA	9/93	WAP
			F	REV 0600-5641-96 TT	9-97	WAP
			G	REV PER OH14-0208-05	1-06	PY
			H	REV PER ECD-07-004569	3-07	PY




- △ AMP, DATE CODE, AND PART NUMBER MARKED THIS AREA.
△ HOUSING MATERIAL: POLYPHENYLENE SULFIDE GST-40F, PER MIL-M-24519.
△ CONTACT MATERIAL-BERYLLIUM COPPER (BeCu) OR COPPER NICKEL SILICONE (CuNiSi)
△ FINISH-.000030 GOLD OVER .000030 NICKEL IN CONTACT AREA, .0001 TIN-LEAD ON SOLDER TAILS.
△ LETTERS INDICATING OUTSIDE ROWS AND NUMBERS INDICATING END CAVITIES MARKED THIS SURFACE.
△ LINES INDICATING EVERY FIVE CAVITIES MARKED ON MATING FACE.
△ FINISH: .000030 GOLD OVER .000030 NICKEL IN CONTACT AREA, .0001 TIN ON SOLDER TAILS.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±.010		CONTRACT NO DR Debra Kelly 8-6-79 CHK W. H. Fitchard, Jr. 9/14/79 APPD W. H. Fitchard, Jr. 9/14/79 APPD W. H. Fitchard, Jr. 9/14/79 DSGN APPD OTHER APPD		PART NO	
MATERIAL △ 2/3		NAME RECEPTACLE ASSY, .100C, 3 ROW W/ MOUNTING EARS, BOX CONTACT, SOLDER TAIL		REV H	
FINISH △ 4/1		SIZE CODE IDENT NO DRAWING NO C 00779 531138		SHEET 1 OF 2	
		SCALE 5:1			

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

		REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED	
[SEE SHEET 1 J]							



P.C. BOARD LAYOUT
(FLOW SOLDER TYPE)

4.900	49	5.024	5.125	5.450	5.750	150	5-531138-4
3.400	34	3.524	3.625	3.950	4.250	105	5-531138-2
2.900	29	3.024	3.125	3.450	3.750	90	5-531138-1
1.500	15	1.624	1.725	2.050	2.350	48	1-531138-6
9.900	99	10.024	10.125	10.450	10.750	300	1-531138-5
8.900	89	9.024	9.125	9.450	9.750	270	1-531138-4
6.400	64	6.524	6.625	6.950	7.250	195	1-531138-3
4.400	44	4.524	4.625	4.950	5.250	135	1-531138-2
3.200	32	3.324	3.425	3.750	4.050	99	1-531138-1
4.100	41	4.224	4.325	4.650	4.950	126	1-531138-0
4.000	40	4.124	4.225	4.550	4.850	123	1-531138-9
7.900	79	8.024	8.125	8.450	8.750	240	1-531138-8
6.900	69	7.024	7.125	7.450	7.750	210	1-531138-7
5.900	59	6.024	6.125	6.450	6.750	180	1-531138-6
5.400	54	5.524	5.625	5.950	6.250	165	1-531138-5
4.900	49	5.024	5.125	5.450	5.750	150	1-531138-4
3.900	39	4.024	4.125	4.450	4.750	120	1-531138-3
3.400	34	3.524	3.625	3.950	4.250	105	1-531138-2
2.900	29	3.024	3.125	3.450	3.750	90	1-531138-1

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .010 ANGLES ± .010	CONTRACT NO DR Debra Kelly 8-6-79 CHK W. H. Pritchard Jr. 9/14/79 APPD W. H. Pritchard Jr. 9/14/79 APPD D. Zentgraf 9/14/79 DSGN APPD OTHER APPD	AMP INCORPORATED Harrisburg, Pa. NAME RECEPTACLE ASS'Y, .100 @, 3 ROW, W/ MOUNTING EARS, BOX CONTACT, SOLDER TAIL SIZE CODE IDENT NO DRAWING NO C 00779 531138 SCALE 5:1 SHEET 2	
MATERIAL 2 3	FINISH 4 7	NO. OF POSITIONS PART NO	