




FEATURES:

- Ideal for temporary connection between terminals, wire wrap posts and test equipment.
- Banana Plug is vertically stackable and cross stackable.
- Banana Plug will mate to Model #5259, 1581 or any standard Banana Jack.

MATERIALS:

Connector: 1st End – Minipincer Test Clip

Material: Selectively gold plated Beryllium Copper contact.

Insulation: Nylon

Wire: 20 AWG, 41 x 36 t.c., PVC insulated, 2.2 (.087) O.D.

Marking: "POMONA 5421-XX-"

Connector: 2nd End – Stacking Banana Plug

Material: Brass Body, Beryllium Copper spring, nickel plated.

Insulation: Polypropylene

RATINGS:

Operating Temperature.: +55°C. (+ 131°F.) Max.

Voltage: Hand-held testing: 30 VAC/60 VDC Max.

Hands free testing in controlled voltage environments: 300 WVDC

Current: 5 Amperes

ORDERING INFORMATION: Model 5421-XX-*

XX = Cable Lengths, Standard Lengths: 12" (305), 18" (457), 24" (610) 36" (914), 48" (1219) & 60" (1524).

Additional lengths can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: 5421-60-2 Indicates 60" in length, Color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA