




3.5mm 4 Pole Stereo Jack



161-5350

KOBICONN

3.5mm 4 Pole Stereo Jack



NOTE: ±0.2 FOR PCB LAYOUT



Dimensions: mm (In.)

SPECIFICATIONS	
Housing:	PA66 Black
Terminals:	Phosphor bronze tin plated
Ground Terminal:	Phosphor bronze gold plated
Insertion/ Ext Force:	.3-3 Kgs
Dielectric Strength:	500 VAC for 1 min.
Insulation Resistance:	100 M ohm minimum
Contact Resistance:	50 m ohm maximum
Life Cycle:	5000 matings minimum
Operating Temperature:	-25°C to +85°C
Voltage Rating:	16.0 VDC
Current Rating:	0.3 A

Date Last Revised: 10-15-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300496

161-5350

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-5350](#)