



Scotchmate™ Hook and Loop and Dual Lock™ Reclosable Fasteners

Product Information

June, 1997

Product Description

3M™ Scotchmate Hook and Loop and 3M™ Dual Lock Reclosable Fastening Systems offer advanced closure alternatives to zippers, screws, snaps, hooks, bolts and more. They're often better than conventional closure methods because they offer greater design flexibility, faster product assembly, smoother and cleaner exterior surfaces and improved product performance in many applications.

Mini Packs are great for design development and small volume product requirements. Now you can inexpensively test and evaluate 3M's seven most popular reclosable fastening systems before making a more substantial investment. Mini Packs also simplify storage and dispensing.

Available in Mini Packs are both plain-backed sew-on and adhesive-backed fasteners which allow for faster, easier attachment. Pressure-sensitive adhesive-backed versions include both general purpose and 3M high performance adhesive.



Scotchmate Hook and Loop Fasteners

Product/Color	Roll Size	Description	Temperature
MP-3401/02 white	1 in x 4.9 yds/1 ea	Sew-on Scotchmate Fastener	250°F Continuous (121°C)
MP-3401/02 black	1 in x 4.9 yds/1 ea	Sew-on Scotchmate Fastener	250°F Continuous (121°C)
MP-3526/27 white	1 in x 4.9 yds/1 ea	General Purpose Pressure-Sensitive Rubber Adhesive/Bonds to Most Surfaces	120°F (49°C) Continuous 158°F (70°C) Intermittent
MP-3526/27 white	1 in x 4.9 yds/1 ea	General Purpose Pressure-Sensitive Rubber Adhesive/Bonds to Most Surfaces	120°F (49°C) Continuous 158°F (70°C) Intermittent

Dual Lock Reclosable Fasteners

Product/Color	Roll Size	Description	Temperature
MP-3541/42 black	1 in x 4.9 yds/1 ea	General Purpose Pressure-Sensitive Rubber Adhesive/Bonds to Most Surfaces	120°F (49°C) Continuous 158°F (70°C) Intermittent
MP-3551/52 black	1 in x 4.9 yds/1 ea	High Performance Acrylic Pressure Sensitive Adhesive UV and Plasticizer Resistant	158°F (70°C) Continuous 200°F (93°C) Intermittent
MP-3560 clear	(2) 1 in x 4.9 yds	CLEAR Dual Lock High Performance Adhesive UV and Plasticizer Acrylic Resistant	158°F (70°C) Continuous 200°F (93°C) Intermittent

3M™ Scotchmate™ Hook and Loop and 3M™ Dual Lock™ Reclosable Fasteners

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550. Address correspondence to: 3M Industrial Tape and Specialties Division, 3M Center, Building 220-7E-01, St. Paul, MN 55144-1000. Our fax number is 612-733-9175. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-809-750-3000. In Mexico, phone: 5-728-2180.

Important Notice

3M MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of application. Please remember that many factors can affect the use and performance of a 3M ITSD product in a particular application. The materials to be bonded with the product, the surface preparation of those materials, the product selected for use, the conditions in which the product is used, and the time and environmental conditions in which the product is expected to perform are among the many factors that can affect the use and performance of a 3M ITSD product. Given the variety of factors that can affect the use and performance of a 3M ITSD product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M ITSD product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Limitation of Remedies and Liability

If the 3M product is proved to be defective, THE EXCLUSIVE REMEDY, AT 3M'S OPTION, SHALL BE TO REFUND THE PURCHASE PRICE OF OR TO REPAIR OR REPLACE THE DEFECTIVE 3M PRODUCT. 3M shall not otherwise be liable for loss or damages, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including negligence, warranty, or strict liability.

ISO 9002

This Industrial Tape and Specialties Division product was manufactured under a 3M quality system registered to ISO 9002 standards.



Industrial Tape and Specialties Division

3M Center, Building 220-7E-01
St. Paul, MN 55144-1000



Recycled Paper
40% pre-consumer
10% post-consumer

Printed in U.S.A.
©3M 1997 70-0704-5646-5