

- For use with Alcatel's DynaMiTe MTK-20140 ADSL chipset
- Excellent THD performance
- Small footprint

Electrical Specifications @ 25°C - Operating Temperature -40°C to +85°C

Part Number	Application	Mounting	Turns Ratio (±2%) (1-4):(10-7)	OCL @ 10 kHz, 0.1 V (1-4) with (2-3) shorted	Leakage Inductance @ 300 KHz, 0.1 V (1-4) with (2-3), (7-10) and (8-9) shorted	Longitudinal Balance (from 30 KHz to 1.1 MHz)
B2068	CO	THT	2:1 (Line to Chip)	410 μH (± 10%)	6.5 μH MAX	-40 dB MIN
B2064 ²	CPE	SMT	1:1 (Line to Chip)	480 μH (± 10%)	10.0 μH MAX	-40 dB MIN

Additional Specifications


Part Number	THD (Linearity - Typical)	DC Resistance (1-4) (w/2-3 shorted)	Isolation Voltage (Vrms)	Insertional Loss ¹ (@ 100 KHz and 1.1 MHz)
B2068	CO	THT	2:1 (Line to Chip)	-40 dB MIN
B2064 ²	CPE	SMT	1:1 (Line to Chip)	-40 dB MIN

¹ Frequency Response: 0.5 dB MAX, from 100 KHz to 1.1 MHz.; -1.5 dB MAX from 30 KHz to 100 KHz


² Transformers are shipped in tubes unless tape and reel is specified. Please add the suffix "T" (i.e. B2064T) for tape and reel orders.

Mechanicals

B2068



B264



Weight6.2 grams
Tray60/tray

Dimensions: $\frac{\text{Inches}}{\text{mm}}$ Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

USA 858 674 8100

Germany 49 7032 7806 0

Singapore 65 6287 8998


Shanghai 86 21 62787060

China 86 755 33966678

Taiwan 886 3 4356768

ADSL Line Transformers

Schematic



For More Information

Pulse Worldwide Headquarters

12220 World Trade Drive
San Diego, CA
92128
U.S.A.

Tel: 858 674 8100
Fax: 858 674 8262

Pulse Europe

Einsteinstrasse 1
D-71083 Herrenberg
Germany

Tel: 49 7032 78060
Fax: 49 7032 7806 135

Pulse China Headquarters

B402, Shenzhen Academy of
Aerospace Technology Bldg.
10th Kejian Road
High-Tech Zone
Nanshan District
Shenzhen, PR China
518057
Tel: 86 755 33966678
Fax: 86 755 33966700

Pulse North China

Room 2704/2705
Super Ocean Finance
Ctr.
2067 Yan An Road
West
Shanghai 200336
China

Tel: 86 21 62787060
Fax: 86 2162786973

Pulse South Asia

135 Joo Seng Road
#03-02
PM Industrial Bldg.
Singapore 368363

Tel: 65 6287 8998
Fax: 65 6287 8998

Pulse North Asia

3F, No. 198
Zhongyuan Road
Zhongli City
Taoyuan County 320
Taiwan R. O. C.
Tel: 886 3 4356768
Fax: 886 3 4356823 (Pulse)
Fax: 886 3 4356820 (FRE)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2012. Pulse Electronics, Inc. All rights reserved.