




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4251-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4251-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
- SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCK WASHER.

3,000	125 VDC	10 GΩ	500 VDC	15 A	10	30	65	65
MIN. CAP.(pf)	+125 °C DC WORKING VOLTAGE	I.R. MIN. @ 100 VDC	DWV	CURRENT	10 MHz	100 MHz	1 GHz	10 GHz
MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220								

X-2015 Rev-0	REVISION RECORD			Title MULTI LAYER BUSHING STYLE EMI FILTER	Drawn S. M. 06-03-02		Scale 4 X	
	Original Release	0						
	C.O. 6611							
	DIM. REVISED 6.76 WAS 6.75. E.C. 5-26-92				1	RDN TO COMP FMT. S.M. 06-03-02		
	6667							
	20020528-3-01	2						
	ADDED NOTES 1-3. S.M. 10-06-05							
	20050927-7-02				3			
				--TOLERANCES-- Unless Otherwise Specified				
				DECIMAL ± .031 [0.79]				
				ANGLES ±				
				TUSONIX TUCSON, ARIZONA		Approved J.Mc. 06-03-02		
						A	4251-000	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4251-000LF](#)