

P48 North American Wall Mount 5.75-14.0 Watt Series

Features

- 120 VAC Input
- North American Wall Plug Style
- Rated for Continuous Duty
- Filtered
- Unregulated Outputs up to 12 Watts
- Meets Safety Agency Requirements

- Impact Resistant Polycarbonate Enclosure
- Private Label Marking Available
- 1 Year Warranty
- Modified and Custom Designs Also Available
- Manufactured in China

Ault Model	Rated Output Volts DC	Maximum Current-Amps	Maximum Watts
P48-051150-A000G	5	1.15	5.75
P48-061500-A000G	6	1.50	9.0
P48-071500-A000G	7	1.50	10.5
P48-081200-A000G	8	1.20	9.6
P48-091000-A000G	9	1.00	9.0
P48-100800-A000G	10	0.80	8.0
P48-120600-A000G	12	0.60	7.2
P48-120800-A000G	12	0.80	9.6
P48-120850-A000G	12	0.85	10.2
P48-121000-A000G	12	1.00	12.0
P48-121200-A000G	12	1.20	14.4
P48-150600-A000G	15	0.60	9.0
P48-150800-A000G	15	0.80	12.0
P48-151000-A000G	15	1.00	15.0
P48-180667-A000G	18	0.67	12.0
P48-210571-A000G	21	0.57	12.0
P48-220545-A000G	22	0.54	12.0
P48-240250-A000G	24	0.25	6.0
P48-240500-A000G	24	0.50	12.0

Input

- Voltage 120 VAC
- Line Frequency 60 Hz
- Connector North American Wall Plug, No Ground

Electrical

- Topology DC Unregulated Power Supply
- Dielectric Withstand 1500 VAC primary - secondary
1500 VAC primary-core
500 VAC secondary-core
- Protection Current, Thermal or Energy Limiting
- EMI Meets FCC Class B

Safety Approvals

- Safety Agencies UL1310, CSA22.2-223

Environmental

- Operating Temperature 0° to 40° C with no derating
- Storage Temperature -30° to +85° C
- Relative Humidity 5% to 95% non-condensing

- Altitude 0-10,000 feet
- Cooling Convectional - non vented case

Mechanical

- Case Dimensions P48- North American Wall Plug
2.5 L x 2.2 W x 2.0 H (in)
63 L x 57 W x 50 H (mm)
- Case Material Black 94 V1 Polycarbonate
- Weight 17 ounces, 475 grams, (excluding cord)
- Cord and Connector 6 ft., 2 Conductor, 22-24 AWG
Ault #3 Connector
Other Connectors Available

**UL 1950

ONE YEAR WARRANTY

Ault Incorporated, 7105 Northland Terrace, Minneapolis, MN 55428

Contact Ault Inc. for all your custom design requirements. Phone: 763.592.1900 · Fax 763.592.1911

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SL Power:](#)

[P48240500A300G](#)