

Anna-50-7 series




Ordering number	C11670		
Description	C11670_Ann-50-7-S-OSL		
Family	Anna-50-7	FWHM	0 degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



Ordering number	C11679		
Description	C11679_Ann-50-7-M-OSL		
Family	Anna-50-7	FWHM	0 degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



Ordering number	C11682		
Description	C11682_Ann-50-7-W-OSL		
Family	Anna-50-7	FWHM	0 degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



L
T
F
F
e
i
n
d

DRAWING TITLE

Datasheet Anna50-series Lens

DRAWN BY
p

DATE
05.10.2010

CHECKED BY
t k

DATE
03.08.2010

DESIGNED BY
hh

DATE
30.07.2010

SIZE A4	DRAWING NUMBER -	REV 1
SCALE 1 : 1	WEIGHT (g)	SHEET 1 / 1