


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300500512](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Brad RJ-Lnxx RJ-45 568B Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 24 AWG, PUR Cable, 1.0m (3.28') Length



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Cordsets
Series	130050
Connector End A	RJ-45 (standard)
Connector End B	RJ-45 (standard)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Industrial Ethernet Solutions
Performance Category	5e
Product Name	Brad, RJ-Lnxx
Protocol	N/A
Region	America, Asia, Europe
Type	Double Ended
UPC	78172504549

Physical	
Cable Diameter	6.35mm (.250")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	N/A
Gender	Male-Male
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PVC
Material - Coupling Nut	N/A
Material - Plating Mating	N/A
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	24
Wire/Cable Type	Shielded-Twisted Pair

Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Material Info	
Engineering Number	ENV3335M010

Reference - Drawing Numbers	
Sales Drawing	SD-130050-021

<u>EU ELV</u> Not Reviewed	
<u>EU RoHS</u> Not Reviewed	<u>China RoHS</u>
<u>REACH SVHC</u> Not Reviewed	
<u>Halogen-Free</u> <u>Status</u> Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130050](#) Series