




- △ HOUSING: LCP, GLASS FILLED, COLOR: BLACK.
- △ CONTACT: BERYLLIUM COPPER.
- △ DIMENSION IN REFERENCE TO LOWEST POINT OF EACH LEAD.
4. POINT OF CONTACT 2.3[.091] REF FROM MATING FACE.
- △ APPLIES TO ALL SOLDER TAILS.
- △ PACKAGED IN 56mm WIDE TAPE AND REEL.
- △ PACKAGED IN 72mm WIDE TAPE AND PLASTIC REEL.
- △ CONTACTS: 0.00076[.000030] MINIMUM GOLD ON MATING AREA 0.00064[.000025] MINIMUM SEMI-BRIGHT NICKEL ON MATING AREA 0.00254[.000100] MINIMUM MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [0.000050] MATTE NICKEL.

**COPYRIGHT 2005
TYCO ELECTRONICS CORP
ALL RIGHTS RESERVED**

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
A. FERNANDEZ-DOCK5
02-21-05

CHK
S. BOLASH
02-21-05

APVD
M. WALMSLEY
02-21-05

NAME
RECEPTACLE ASSEMBLY,
SURFACE MOUNT, 68 POSITION,
ZERO OFFSET, AMP MEMORY CARD

SIZE
A1

CAGE CODE
00779

DRAWING NO
5146228

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
5:1

SHEET
1 OF 1

REV
A1

OBsolete

△

5146228-4

△

5146228-3

△

TE Connectivity

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± 0.13[.005]

4 PLC ± —

ANGLES ± 0° 30'

FINISH