

JST

Hand crimping tool
Type: WC-260

Features

Parallel action
operation

Ratchet release

Easy readjustment
of load

Contact locator with
insulation-stop

Precisely ground
profiles

Ergonomic soft grips
colour: green

Fully recyclable

Applicable terminal:
< >EH-001T-0.6

Cross section range:

Profile 1: 30 AWG

Profile 2: 26 AWG/28 AWG


Profile 3: 22 AWG/24 AWG

Crimp height specification

30 AWG - 0.57-0.62mm



28 AWG - 0.60-0.65mm

26 AWG - 0.60-0.70mm





OPERATION INSTRUCTIONS

1. Open flap locator and insert contact up to stop.
2. Close flap locator.



3. Close handtool until first ratchet.
4. Insert wire up to stop.



5. Close handtool until the ratchet releases.
6. Open flap locator and carefully remove the wire.