

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39880-1209](#)
Status: **Active**
Overview: Eurostyle™ Terminal Blocks
Description: 5.08mm Pitch Horizontal Fixed Mount PCB Terminal Block, 9 Circuits

Documents:
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR25562
UL E48521

General

Product Family Terminal Blocks
Series [39880](#)
Application N/A
Component Type One Piece
Overview [Eurostyle™ Terminal Blocks](#)
Product Name Eurostyle™ Fixed Mount
Type Euro Block
UPC 800756723846

Physical

Circuits (Loaded) 9
Circuits (maximum) 9
Entry Angle 90° Angle
Flammability 94V-0
Lock to Mating Part None
Number of Rows 1
Orientation Horizontal
PC Tail Length 3.60mm
PCB Retention None
PCB Thickness - Recommended 1.57mm
Panel Mount No
Pitch - Mating Interface 5.08mm
Pitch - Termination Interface 5.08mm
Polarized to Mating Part Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +105°C
Wire Size AWG 12, 14, 16, 18, 20, 22, 24, 26, 28, 30


Electrical

Current - Maximum per Contact 17.5A
Voltage - Maximum 300V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-39880-011



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[39880Series](#)