



MOP650GA

Colour CMOS Camera With Microphone



High Resolution Picture - 380TVL

Compact Size

Low Power Consumption

High Sensitivity

Microphone




Specifications:

Signal	PAL (NTSC available)
Sensor	1/3 Interline CMOS
Number of Pixels	628 X 582
Scanning	2:1 Interlace
Synchronisation	Internal
Resolution	380TV lines
Video Out Level	1.0Vp-p/75ohm composite
S/N	46dBMin.
Lens information	3.6mm/F2.0 92 degree
Minimum Illumination	3 Lux (f1.4)
Gamma Correction	0.45
Working temperature	-10 to 45 °C
Electrical Shutter	1/50 ~ 1/15000 Sec
Power Supply Voltage	DC12V
Power Supply Current	50mA Max.

Dimensions

RCA male yellow for video output
RCA male white for audio output



Input DC Plug Female For Power Input
Center(+),Outer(-)