



TW-20-03-L-Q-400-085

TW-08-09-F-T-165-100

TW-16-06-T-D-500-100

TW SERIES

THROUGH-HOLE BOARD STACKERS

Choice of one through six rows

TW

NO. PINS PER ROW

LEAD STYLE

PLATING OPTION

ROW OPTION

STACKER HEIGHT

TAIL SPEC

02 thru 50

Specify
LEAD STYLE
from
chart
below.

-F
= Gold flash
on post,
Matte Tin on tail

-L
= 10μ" (0,25 μm)
Gold on post,
Matte Tin on tail

-T
= Matte Tin

-S
= Single
Row

-D
= Double
Row

-T
= Triple
Row

-Q
= Four
Row

-5
= Five
Row

-6
= Six
Row

-“XXX”
= Stacker
Height
in inches
(0,13 mm) .005”
increments
Example: -250
= (6,35 mm)
.250”

LEAD STYLE	OAL
-01	(8,20) .323
-02	(9,60) .377
-03	(13,60) .535
-04	(14,10) .555
-05	(15,10) .594
-06	(17,10) .673
-07	(19,10) .751
-08	(21,10) .830
-09	(11,60) .456
-10	(15,60) .614
-11	(10,08) .397
-12	(28,19) 1.110

-“XXX”
= Tail Length
in inches
(0,13 mm) .005”
increments
Example: -150
= (3,81 mm)
.150”

-“XXX”
= Polarized
Position
(Specify
position to
be removed)

ROW OPTION	STACKER HEIGHT
-S, -D*, & -Q	(3,05) .120 MIN
-T, -5, -6	(4,06) .160 MIN

* -D with stacker height greater than (4,06 mm) .160” will not have standoffs.

*-D with stacker height greater than (4,06 mm) .160" will not have standoffs.