

Path: [Home](#) > [Enclosure Index](#) > [ROLEC-HAMMOND Aluminum Product Index](#) > **R190 & R191 Series**



[click to enlarge](#)



[click to enlarge](#)

Key Features:

- Modern, high quality instrument enclosure
- Material - Aluminum die-cast: GD SI 12 / DIN 1725
- Shallow lid, deep body
- Captive stainless steel lid screws
- Enclosure can be mounted after closing lid
- Integrated 1.7 mm recess in lid for membrane keypads and front panels
- Neoprene oil and petrol resistant - thermoplastic gasket standard. (-40°C up to +120°C)
- Clip-on design covers - to hide mounting & lid screws (plastic - polyoxymethylene) - grey RAL 7040
- Complete with lid captivation devices
- Degree of protection: NEMA 4X, IP67
- Textured polyester powder coat, grey RAL 7040. (can be supplied unpainted on special order)
-  Link here to [photo tables](#) of each part number

Part No.	 Reader File	 AutoCAD .dxf File	 3D Solid Model .igs & .stp files (zipped)	Units	Width	Length	Depth (Including Lid)
					A	B	C
R191-052-000	 752K	 220K	 266K	mm	50	75	33
				inches	1.9	2.9	1.3
R191-054-000	 735K	 216K	 266K	mm	50	100	33
				inches	1.9	3.9	1.3
R191-070-000	 	 	 	mm	70	100	50

	803K	220K	313K	inches	2.7	3.9	1.9
R191-090-000	 1,082K	 648K	 7.78M	mm	90	120	60
				inches	3.5	4.7	2.4
R191-072-000	 691K	 219K	 314K	mm	70	140	50
				inches	2.7	5.5	1.9
R190-110-000	 1,013K	 672K	 7.67M	mm	110	140	60
				inches	4.3	5.5	2.4
R191-092-000	 1,009K	 658K	 7.80M	mm	90	160	60
				inches	3.5	6.3	2.4
R190-130-000	 956K	 735K	 7.71M	mm	130	160	70
				inches	5.1	6.3	2.8
R191-074-000	 687K	 220K	 314K	mm	70	180	50
				inches	2.7	7.1	1.9
R190-150-000	 932K	 726K	 7.67M	mm	150	180	60
				inches	5.9	7.1	2.4
R191-150-000	 1,465K	 651K	 7.80M	mm	150	180	90
				inches	5.9	7.1	3.5
R190-112-000	 929K	 715K	 7.66M	mm	110	200	60
				inches	4.3	7.9	2.4
R190-170-000	 909K	 717K	 7.59M	mm	170	200	60
				inches	6.7	7.9	2.4
R191-170-000	 910K	 646K	 7.74M	mm	170	200	90
				inches	6.7	7.9	3.5
R190-132-000	 886K	 725K	 7.67M	mm	130	220	70
				inches	5.1	8.7	2.8
R191-200-100	 916K	 267K	 1.32M	mm	200	230	120
				inches	7.9	9.1	4.7
R191-094-000	 640K	 242K	 386K	mm	90	250	60
				inches	3.5	9.8	2.4
R190-152-000	 879K	 726K	 7.57M	mm	150	260	60
				inches	5.9	10.2	2.4
R191-152-000	 864K	 655K	 7.70M	mm	150	260	90
				inches	5.9	10.2	3.5
R190-172-000	 865K	 720K	 7.51M	mm	170	280	60
				inches	6.7	11	2.4

R191-172-000	 866K	 638K	 7.67M	mm	170	280	90
				inches	6.7	11	3.5
R191-202-100	 668K	 193K	 437K	mm	200	330	120
				inches	7.9	13.0	4.7



Link here to [photo tables](#) of each part number

Features (by photos):



[click to enlarge](#)

Snap in design covers
hide both lid screws and
installation holes




[click to enlarge](#)

Includes optional use lid
captivation straps



[click to enlarge](#)

Enclosure can be installed
after closing lid



[click to enlarge](#)

Dual channel construction
Mounting holes accessible
with lid closed. All holes
outside of gasket seal.

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check
and ordering!!!

Our Distributors

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)

Copyright; © 2002-2010 Hammond Mfg Co Inc

URL: <http://www.hammondmfg.com>