



13	12	11	10	9
PART NUMBER	ENGINEERING NO.	LENGTH		
1300070071	207000A01F030	3' 0" +1.75 - 0 [.9M +44.5 - 0]		
1300070073	207000A01F060	6' 0" +2.19 - 0 [1.8M +55.6 - 0]		
1300070076	207000A01F120	12' 0" +3.50 - 0 [3.7M +88.9 - 0]		
1300070080	207000A01F200	20' 0" +6.50 - 0 [6.1M +165.1 - 0]		

(A1)



Section Z-Z

NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. CABLE ASSEMBLIES ARE BAGGED SEPERATELY IN POLY BAGS WITH BARCODE LABEL ATTACHED TO OUTSIDE OF BAG
4. WRAP LABEL IS MARKED WITH P/N, DATE CODE VOLTAGE & AMPERAGE
5. MATES WITH: MINI CHANGE, B-SIZE 7 POLE RECEPTACLE
6. ELECTRICAL SPECIFICATIONS:
VOLTAGE RATING: 600V
CURRENT RATING: 8 AMPS
7. ASSEMBLY IS RoHS COMPLIANT

S1	
1	WHITE/BLACK
2	BLACK
3	WHITE
4	RED
5	ORANGE
6	BLUE
7	GREEN/YELLOW

WIRING DIAGRAM

8	1	LABEL	PLASTIC FILM	BLACK/YELLOW
7	1	OVERMOLD	PVC	YELLOW
6	1	COUPLING NUT	ZIN DIE CAST	BLACK
5	1	FRICITION RING	NYON	NATURAL
4	7	SOCKET CONTACT	BRASS	GOLD PLATED
3	7	SOCKET SLEEVE	STAINLESS STEEL	
2	1	INSERT, FEMALE, 7 POLE	PVC	YELLOW
1	1	CABLE, 16-7 ST00W/ST	PVC JACKET	YELLOW
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH


RELEASED
EC NO: WNA2009-0867
DRAWN:BRUPERT 2009/06/25
CHKD:BRUPERT
APPR:JF MURPHY 2009/07/08
REV
A1

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± --- ± .01
1 PLACE ± 0.3 ± ---
ANGULAR ±1/2°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM
DRAWN BY DATE
BRUPERT 2009/04/02
CHECKED BY DATE
B.WOODMAN 2009/04/03
APPROVED BY DATE
J.MURPHY 2008/04/06
MATERIAL NO.
SEE CHART
SIZE C

SCALE 1:1
DESIGN UNITS INCH
THIRD ANGLE PROJECTION
TITLE
MINI-CHANGE CORD ASSY
FEMALE, B-SIZE
7 POLE
MOLEX INCORPORATED
DOCUMENT NO.
SD-130007-005
SHEET NO.
1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300070080](#)