




SLB500/SLW500




SLB150/SLW150



SLW2000/SLB2000


SLB500 500W PIR Halogen Floodlight - Black SLW500 500W PIR Halogen Floodlight - White

- Powerful 500W enclosed halogen floodlight with adjustable integral PIR detector.
- Can replace an existing outdoor light.
- Detects body heat up to 12 metres away and automatically switches the light ON.
- 140° adjustable detection angle.
- Moveable detector allows horizontal and vertical PIR range adjustment.
- Manual ON/OFF switching override.
- Light-ON time adjustable from 5 seconds to 5 minutes.
- Built-in sensor prevents daytime operation.
- 500W halogen lamp supplied.
- IP44 weatherproof rating.
- Total PIR Switching: 2000W incandescent or halogen, 500W fluorescent, 22W low energy.



SLB2000 2000W PIR Light Controller - Black SLW2000 2000W PIR Light Controller - White

- Powerful PIR controller for new and existing installations.
- 12m detection range with 140° area of detection.
- Light ON times adjustable from 5 seconds to 5 minutes.
- Adjustable light level control.
- Manual ON/OFF switching override.
- Quick & easy installation.
- IP44 weatherproof rating.
- Total PIR Switching: 2000W incandescent or halogen, 500W fluorescent, 22W low energy.



CFB500/CFB150 Matching Floodlights for SLB Range - Black CFW500/CFW150 Matching Floodlights for SLW Range - White

- CFB500 - 500W for SLB500 - Black.
- CFW500 - 500W for SLW500 - White.
- CFB150 - 150W for SLB150 - Black.
- CFW150 - 150W for SLW150 - White.



CFB500/CFW500



CFB150/CFW150

SLB150 150W PIR Halogen Floodlight - Black SLW150 150W PIR Halogen Floodlight - White

The SLB150/SLW150 share all the features and benefits of the SLB500/SLW500 except for the use of 150W halogen bulbs.

- Compact 150W enclosed halogen floodlight with adjustable integral PIR detector.
- 150W halogen lamp supplied.
- Total PIR Switching: 2000W incandescent or halogen, 500W fluorescent, 22W low energy.



Product Specifications

	SLB500	SLW500	SLB150	SLW150	SLB2000	SLW2000
Operating Voltage	230V AC	•	•	•	•	•
Maximum Light Load (W)	Internal 500	500	150	150	•	•
Tungsten/Halogen	External 1500	1500	1850	1850	2000	2000
Maximum Fusing	13A	13A	13A	13A	13A	13A
Weatherproof Rating	IP44	IP44	IP44	IP44	IP44	IP44
Detection Range (Max)	Metres 12	12	12	12	12	12
Angle of Detection	140°	140°	140°	140°	140°	140°
Light On Time After last detection (Adjustable)	Seconds (Min) 5	5	5	5	5	5
Minutes (Max)	5	5	5	5	5	5
Permanent ON Facility (Electronic)	•	•	•	•	•	•
Adjustable Light Level Control	•	•	•	•	•	•
Conforms to	73/23/EEC	•	•	•	•	•
Directives	89/336/EEC	•	•	•	•	•
Overall Dimensions (mm)	Height 250	250	200	200	150	150
Width	190	190	140	140	70	70
Depth	170	170	170	170	115	115

Note: All 'SLB/SLW' products with exception of SLB44/SLW45 can be wired in parallel to enable any detector to turn ON all of the lights connected to it (the total wattage capability of the unit must not be exceeded).