



AC Power Supply – 12VDC, 100/240VAC, 0.5A, non-locking barrel (US only)

PART NUMBER: 76000737

INPUT SPECIFICATIONS

Rated input voltage range: **100-240VAC**

Input frequency: **47-63Hz**

Rated input current: **0.3A max at 100VAC**

Max. in-rush current: **80A / 1msec.**

Input Plug Type: **US**

OUTPUT SPECIFICATIONS

Output Voltage: **12VDC**

Load current: **.5A (0A to .83A)**

OUTPUT PLUG

Connector Type: ***Non-locking barrel plug***

Outer Diameter: **5.5mm**

Inner Diameter: **2.1mm**

ENVIRONMENT

Operating Temperature: **0° C to 40° C**

Storage Temperature: **-20° C to 65° C**

Certifications: ***FCC, cUL, UL1950***

DIMENSIONS

Size (LxHxW): **46 x 27 x 62mm**

Weight: **220g**

Cord Length: **1800mm"**