

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0873600005](#)
Status: **Obsolete**
Description: 3-in-1 Combo Connector
Wide SCSI/2.00mm/Power, Right Angle, 4|12|68 Circuits
Replacement Part Number: NO REPLACEMENT PART AVAILABLE

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	87360
Application	Wire-to-Board
Component Type	Plug, Receptacle
Obsolete Date	2003/12/01
Product Name	3-in-1 Combo, SCSI+
Replacement Part Number	NO REPLACEMENT PART AVAILABLE
Type	N/A

Physical

Circuits (Loaded)	84
Circuits (maximum)	84
Durability (mating cycles max)	100
Flammability	94V-0
Lock to Mating Part	None
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Orientation	Right Angle
PCB Retention	Yes
PCB Thickness - Recommended	0.90mm (.035")
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	1.27mm (.050"), 2.00mm (.079"), 5.08mm (.200")
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	2.540µm (100µ")
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1A, 5A
Shielded	Yes
Voltage - Maximum	5V

Material Info

EU RoHS	China RoHS
Compliance Status	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[87360Series](#)

Mates With
2mm shunt/ receptacle, [8981](#) , [70498-2068](#)