



SCHEMATIC



BTS-1102(L)-(OF)-(B)-O-(H)

Operating Force:
1:100±30gf
2:180±30gf
3:250±50gf


Stem Color:
B:Black
(R:Red)

Foundation:
□:3:3.45mm(3.15基座)
2:3.1mm(2.8基座)


Model.No.	1102	1102A	1102AL	1102AA	1102AE	1102B
L(mm)	4.3	5.0	5.5	6.0	6.5	7.0

Model.No.	1102N	1102C	1102Y	1102R	1102D	1102X	1102U	1102L	1102K	1102I	1102O	1102Q
L(mm)	7.5	8.0	8.5	9.0	9.5	10	10.5	11	12	13	14.5	15

Model.No.	1102H	1102HX	1102HZ	1102ZL	1102ZZ
L(mm)	17	18	19	21	26



P.C.B Layout



- 1.Rating: DC12V 50mA
- 2.Contact Resistance:50mΩ max
- 3.Insulation Resistance:100MΩ Min
- 4.Electrically Life:
100gf :100,000 cycles
180gf :80,000 cycles
250gf :60,000 cycles
- 5.Travel:0.25±0.1mm
- 6.General tolerance:±0.1mm

No	NAME	MATERIAL	NATIONALITY	QTY	FINISHING
1	Terminal	Brass	China	1	Silver plating
2	Case	PA66	USA	1	Black
3	Contact	Phosphor bronze	Korea	1	Contact side silver plating
4	Cover	Brass	China	1	CuSn plating
5	Stem	PA66	USA	1	Black L≤9.5mm
		PC	China	1	Black L>9.5mm

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO.	149948	GOLDSUN NO.	BTS-1102B-2-B
Description	"TACT SWITCH BLACK SPST N.O (N.C.) PC LEAD."		Rev. 1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: