





Logic Pulser

PSP-110030



Dimensions: mm

Specifications :

- Tests TTL, DTL, RTL, HTL, CMOS, and MOS
- Produces 10 μ sec pulse signal
- Maximum allowable supply voltage: ± 25 V
- Operating voltage range: +3 V to + 18 V
- Maximum output allowable connection voltage: ± 25 V
- Maximum sync input voltage: ± 120 V/15 sec
- Sync Input impedance: 100 k Ω minimum
- Pulse repetition rate: 0.5 Hz/500 Hz
- Pulse width at pulser output pin: 10 μ sec typical, 100 mA load
- Output current:
 - Pulse mode: 100 mA sink/source
 - 50% pulse mode: 4 mA sink/source
- Power supply protection: ± 25 V/15 sec

Updated: 9-12-07

383-LP20110

Available from Mouser Electronics

1-800-346-6873

www.mouser.com

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

PSP:

[383-LP20110](#)