


Heatsinks for LEDs / **ICK LED R 40 x 27**



$$R_{th} = 9,41 \text{ K/W}$$

Ø 40 x 27 mm, for IC design LED

Parameters of article **ICK LED R 40 x 27**

R_{th} [K/W]	 9.41
dissipation loss [W]	 12.1
mounting method	therm. conductive foil / therm. cond. adhesive
socket	universal
suitable for processor type	universal
Ø [mm]	 40
height [mm]	27
plate thickness [mm]	5
surface treatment	black anodised

Accessories/ related articles

Thermally conductive foil both sides adhesive / **WLFT 404 D 40**

Thermally conductive foil both sides adhesive / **WLFT 405 D 40**