







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
5 (17x)	1 (17x)		A23	REVISED PER ECO-20-003218	05JUN2020	AP	VN
			A24	REVISED PER ECN-24-252480	19FEB2024	V.N.	V.N.
			A25	REVISED PER ECN-24-292433	07NOV2024	RG	VN
			A26	REVISED PER ECN-25-305493	10FEB2025	V.N.	V.N.



SECTION B-B



SECTION C-C



NOTES
(NOTE)

- 1 POLYAMIDE 6.6 GLASS FILLED
PA 66 CARICATO VETRO
- 2 THE CAVITY MASK MUST BE ASSEMBLED WITH
CONNECTOR P/N 284742-1/-2
IL COPERCHIO TAPPA CAVITA' VA ASSEMBLATO CON
IL PORTA CONTATTI COMPLETO P/N 284742-1/-2
- 3 TE CONNECTIVITY LOGO
IN ALTERNATIVE *tyco* LOGO OR  LOGO
(MARCHIO TE CONNECTIVITY
IN ALTERNATIVA MARCHIO *tyco* OPPURE )

POSITION (POSIZIONE)	OPEN CAVITIES CAVITA' APERTE)
-------------------------	----------------------------------

1, 2, 8, 11, 12, 13, 15, 16, 17,
19, 20, 21, 23, 27, 28, 29, 31,
33, 37, 40, 41, 42, 43, 44, 46,
47, 49, 50, 51, 52, 53, 58, 60.


POSITION CLOSED CAVITIES
(POSIZIONE CAVITA' CHIUSE)

3, 4, 5, 6, 7, 9, 10, 14, 18, 22,
24, 25, 26, 30, 32, 34, 35, 36,
38, 39, 45, 48, 54, 55, 56, 57, 59.

OBSOLETE

~~284939-1~~ AS SHOWN
(NERO / BLACK)

APPLICATION (APPLICAZIONE) : IVECO




SCALE 2:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. POLIZZI		 TE Connectivity	
		CHK O. CANUTO			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. GENTA	
mm		0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.2 3 PLC ± 4 PLC ±		NAME CAVITY MASK FOR 60 POS. CONNECTOR (COPERCHIO CAVITA' PER CONNETTORE 60 POSIZIONI)	
		ANGLES FINISH ±1°		PRODUCT SPEC 108-20254 APPLICATION SPEC 411-20067	
MATERIAL		WEIGHT		SIZE	CAGE CODE
		-		A2	00779
		Customer Drawing		DRAWING NO	RESTRICTED TO
				C-284939	-
				SCALE 5:1	SHEET 1 OF 6
				REV A26	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	2007
© COPYRIGHT 2007	Tyco Electronics AMP GmbH	ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
	-		-	SEE SHEET 1			




POSITION OPEN CAVITIES (POSIZIONE CAVITA' APERTE)	POSITION CLOSED CAVITIES (POSIZIONE CAVITA' CHIUSE)
1, 2, 3, 4, 9, 10, 11, 12, 13, 15, 16, 17, 19, 22, 24, 25, 28, 29, 31, 35, 36, 37, 38, 42, 43, 44, 46, 47, 48, 49, 50, 51, 52, 53, 54, 55.	5, 6, 7, 8, 14, 18, 20, 21, 23, 26, 27, 30, 32, 33, 34, 39, 40, 41, 45, 56, 57, 58, 59, 60.




POSITION OPEN CAVITIES (POSIZIONE CAVITA' APERTE)	POSITION CLOSED CAVITIES (POSIZIONE CAVITA' CHIUSE)
1, 2, 6, 7, 8, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 25, 27, 29, 30, 31, 32, 33, 35, 36, 38, 39, 40, 42, 43, 44, 45, 46, 47, 48, 50, 51, 52, 53, 54, 55, 57, 60	3, 4, 5, 9, 10, 24, 26, 28, 34, 37, 41, 49, 56, 58, 59




POSITION OPEN CAVITIES (POSIZIONE CAVITA' APERTE)	POSITION CLOSED CAVITIES (POSIZIONE CAVITA' CHIUSE)
1, 2, 3, 6, 7, 9, 10, 11, 13, 14, 15, 16, 17, 19, 20, 21, 22, 23, 24, 25, 28, 29, 30, 31, 32, 36, 37, 38, 39, 41, 42, 43, 44, 45, 46, 47, 49, 53, 55, 56, 57, 58, 60	4, 5, 8, 12, 18, 26, 27, 33, 34, 35, 40, 48, 50, 51, 52, 54, 59



POSITION OPEN CAVITIES (POSIZIONE CAVITA' APERTE)	POSITION CLOSED CAVITIES (POSIZIONE CAVITA' CHIUSE)
1, 2, 3, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 19, 20, 21, 22, 23, 24, 25, 28, 29, 30, 31, 32, 36, 37, 38, 39, 41, 42, 43, 44, 45, 46, 47, 53, 55, 56, 57, 58, 60.	4, 5, 18, 26, 27, 33, 34, 35, 40, 48, 49, 50, 51, 52, 54, 59



POSITION OPEN CAVITIES (POSIZIONE CAVITA' APERTE)	POSITION CLOSED CAVITIES (POSIZIONE CAVITA' CHIUSE)
1, 2, 8, 11, 12, 13, 15, 16, 17, 19, 20, 21, 22, 23, 26, 27, 28, 29, 30, 31, 33, 37, 39, 40, 41, 42, 43, 44, 46, 47, 49, 50, 51, 52, 53, 56, 57, 58, 59, 60	3, 4, 5, 6, 7, 9, 10, 14, 18, 24, 25, 32, 34, 35, 36, 38, 45, 48, 54, 55



POSITION OPEN CAVITIES (POSIZIONE CAVITA' APERTE)	POSITION CLOSED CAVITIES (POSIZIONE CAVITA' CHIUSE)
1, 2, 6, 8, 11, 12, 13, 16, 17, 19, 20, 21, 22, 23, 26, 27, 28, 29, 30, 31, 33, 35, 37, 39, 40, 41, 42, 43, 44, 45, 46, 47, 49, 50, 51, 52, 53, 56, 57, 58, 59, 60	3, 4, 5, 7, 9, 10, 14, 15, 18, 24, 25, 32, 34, 36, 38, 48, 54, 55


CAVITY MASK APPLICATIONS (APPLICAZIONI COPERCHIO CAVITA')

P/N	284939-3	284939-4	284939-5	284939-6	284939-7	284939-8	284939-9	1-284939-3	1-284939-4	1-284939-5	1-284939-6
APPLICATION (APPLICAZIONE)	1881 B-CAN 1.3 SDE 1881 C-CAN 1.3 SDE 223 1.3 SDE 178 1.3 SDE 350 1.3 SDE 169 1.3 SDE	199 1.3 SDE 90 HP ASTRA 1.3 SDE	COMBO 1.3 SDE CORSA 1.3 SDE	843 1.3 SDE 199 1.3 SDE 70 HP AGILA 1.3 SDE	186, 192, 194, 197, 198, 199, 223, 310, 921, 936, 937, 939, 940, 946, 947, EPSILON, DELTA, AS 101, CORSA, SUV	1.9 JTD 140 CV E3 2.4 JTD 4V 170 CV E3 2.4 JTD 4V 170 CV E3 1881 1.9 JTD 100 HP	156 1.9 JTD 140 CV E3 932 2.4 JTD 4V 170 CV E3 350 1.9 JTD 100 HP	323 1.4 16v TJET 198 1.4 16v TJET	955 (199) 1.4 16v TC (TJET) 312 1.4 16v ABARTH	955 (199) 1.4 16v PDA 310 1.4 16v PDA TATA INDICA 1.4 16v PDA	263 1.4 16v NA 312 1.4 16v NA 848 1.4 16v NA

CAVITY MASK APPLICATIONS (APPLICAZIONI COPERCHIO CAVITA')

P/N	1-284939-8	2-284939-0		2-284939-1	
APPLICATION (APPLICAZIONE)	1.3 SDE 95 HP-1993/9550 S&S 1.3 SDE 95 HP-2630 S&S 1.3 SDE 95 HP-8460 S&S 1.3 SDE 95 HP-3120 S&S ----- 1.3 SDE 75 HP-1993/9550 S&S 1.3 SDE 75 HP-1390 S&S cavities 37, 38, 41 closed with plug (cavità 37, 38, 41 chiuse con tappo)	1.6 MDE 120Hp - 199/199 S&S cavity 15 closed with plug (cavità 15 chiusa con tappo) ----- 1.6 MDE 120Hp - 198/844 1.6 MDE 120Hp - 848 1.6 MDE 120Hp - 955/955 S&S cavities 15, 21 closed with plug (cavità 15, 21 chiuse con tappo) ----- 1.6 MDE 105Hp - 323 cavity 21,22 and 29 closed with plug (cavità 21,22 a 29 chiuse con tappo)	1.6 MDE 105Hp - 263 2.0 BCE 135Hp - 263 cavities 15, 22 and 29 closed with plug (cavità 15, 21 e 29 chiuse con tappo) ----- 1.6 MDE 105Hp - 198/198 TechA 1.6 MDE 105Hp - 940/940 TechA cavities 15, 21, 22 and 29 closed with plug (cavità 15, 21, 22 e 29 chiuse con tappo)	2.0 BCE 170Hp - 939 ----- 2.0 BCE 165Hp - 198/844 2.0 BCE 170Hp - 940/940 TechA cavities 21 closed with plug (cavità 21 chiusa con tappo) ----- 2.0 BCE 180Hp - Saab 9-3 cavities 22, 29 closed with plug (cavità 22, 29 chiuse con tappo)	2.0 BCE 190Hp - 844 cavities 21, 22, 29 closed with plug (cavità 21, 22, 29 chiuse con tappo) ----- 2.0 BCE 140Hp - 940 Tech A cavities 6, 21, 35, 45 closed with plug (cavità 6, 21, 35, 45 chiuse con tappo) ----- 2.0 BCE 135Hp - 196 cavities 6, 21, 22, 29 closed with plug (cavità 6, 21, 22, 29 chiuse con tappo)

P/N		I-284939-7		I-284939-9	
APPLICATION (APPLICAZIONE)		DUCATO EURO 5 FIC		DUCATO EURO 5 FIA	

THIS DRAWING IS A CONTROLLED DOCUMENT.					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±°		DWN M. POLIZZI 25NOV2002 CHR O. CANUTO 25NOV2002 APVD A. GENIA 25NOV2002	
		PRODUCT SPEC 108-20254 APPLICATION SPEC 411-20067		NAME CAVITY MASK FOR 60 POS. CONNECTOR (COPERCHIO CAVITA' PER CONNETTORE 60 POSIZIONI)	
		MATERIAL 		FINISH -	
		WEIGHT -		SIZE A200779	
		CUSTOMER DRAWING Customer Drawing		DRAWING NO C=284939	
		SCALE 5:1		SHEET 4 OF 6	
		REV A2C		RESTRICTED TO -	


 TE Connectivity

