



THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.


DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
X10-0X0		G	ECN C173	01/05/01	K.C.
		H	ADD NOTE 3.0 & CHANGE P/N TO REFLECT ROHS COMPLIANCE PER ECN D811	04/08/05	M.G.




6 CONDUCTOR CABLE



4 CONDUCTOR CABLE




8 CONDUCTOR CABLE



10 CONDUCTOR CABLE

H0043-2000-ND	GLF-120-410-000	4	SILVER SATIN	609.60 M ± 60.96 M [2000 FT ± 200 FT]
H0042-2000-ND	GLF-120-410-010	4	BLACK	609.60 M ± 60.96 M [2000 FT ± 200 FT]
H0041-2000-ND	GLF-120-410-020	4	WHITE	609.60 M ± 60.96 M [2000 FT ± 200 FT]
H0063-1000-ND	GLF-120-610-000	6	SILVER SATIN	304.80 M ± 30.48 M [1000 FT ± 100 FT]
H0062-1000-ND	GLF-120-610-010	6	BLACK	304.80 M ± 30.48 M [1000 FT ± 100 FT]
H0061-1000-ND	GLF-120-610-020	6	WHITE	304.80 M ± 30.48 M [1000 FT ± 100 FT]
H0083-1000-ND	GLF-120-810-000	8	SILVER SATIN	304.80 M ± 30.48 M [1000 FT ± 100 FT]
H0082-1000-ND	GLF-120-810-010	8	BLACK	304.80 M ± 30.48 M [1000 FT ± 100 FT]
H0081-1000-ND	GLF-120-810-020	8	WHITE	304.80 M ± 30.48 M [1000 FT ± 100 FT]
H0103-1000-ND	GLF-120-010-000	10	SILVER SATIN	304.80 M ± 30.48 M [1000 FT ± 100 FT]
H0102-1000-ND	GLF-120-010-010	10	BLACK	304.80 M ± 30.48 M [1000 FT ± 100 FT]
H0101-1000-ND	GLF-120-010-020	10	WHITE	304.80 M ± 30.48 M [1000 FT ± 100 FT]
PART NUMBER DIGI-KEY	PART NUMBER I/O INTERCONNECT	CONDUCTORS NUMBER OF	COLOR	PER REEL STANDARD LENGTH

THIRD ANGLE PROJECTION




UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN MILLIMETER [INCHES]
2) TOLERANCES:
XXX ± 0.25 [0.01]


I/O INTERCONNECT SANTA ANA, CALIFORNIA	
DR. BY JERRY SUN DR. CHECKED	TITLE 26 AWG (7/34) BARE COPPER, NON-UL UNSHIELDED, MODULAR CABLE
REV.	DWG. NO. GLF-120-X10-0X0
ENGINEER	PART NO. GLF-120-X10-0X0
CUST./SALES	CUSTOMER I/O INTERCONNECT
SAV	SCALE: NONE SHEET 1 OF 2

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
X10-0X0		G	ECN C173	01/05/01	K.C.
		H	ADD NOTE 3.0 & CHANGE P/N TO REFLECT ROHS COMPLIANCE PER ECN DB11	04/08/05	M.G.



Ø50.80 ± 6.35
[2.000 ± 0.250]



NOTES: UNLESS OTHERWISE SPECIFIED.

1.0 MATERIAL AND SPECIFICATIONS

1.01 CONDUCTORS: 26 AWG (7/34)
STRANDED BARE COPPER.

1.02 INSULATION: POLYPROPYLENE

1.03 COLOR: PER CALLOUT

2.0 ELECTRICAL CHARACTERISTICS

2.01 TEMPERATURE & VOLTAGE RATING: 80°C 30 V

2.02 CONDUCTORS RESISTANCE: 148 OHMS/KM MAX. AT 20°C

2.03 INSULATION RESISTANCE: 100 MEGAOHMS/KM MIN. AT 20°C

2.04 CAPACITANCE: 15 PF/FT (MAX)

2.05 DIELECTRIC TEST: AC-500V PER 1 MINUTE

2.0 PACKAGING SPECIFICATIONS

2.01 ADD LABEL ON REEL. (SEE LABEL IN
FIGURE 1.)

2.02 PLACE 2 CABLE REEL IN SHIPPING BOX. (SEE
BOX SIZE.)

2.03 MARK BOX WITH PART NUMBER, QUANTITY, WEIGHT,
AND PURCHASE ORDER NUMBER.

3.0 PART TO BE ROHS COMPLIANCE.



FIGURE 1: WHITE BACKGROUND
WITH BLACK LETTERS

4	300.00 [11.811]	150.00 [5.906]	L=12.20" X W=12.20" X H=12.99"
6	250.00 [9.84]	150.00 [5.906]	L=9.84" X W=9.84" X H=12.99"
8	300.00 [11.811]	150.00 [5.906]	L=12.20" X W=12.20" X H=12.99"
10	300.00 [11.811]	180.00 [7.087]	L=12.20" X W=12.20" X H=8.66"
NUMBER OF CONDUCTOR	DIM "A" (REF.)	± 6.35 [0.250] DIM "B"	DIMENSIONS MAX. OUTSIDE SHIPPING BOX

THIRD ANGLE PROJECTION



UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN
MILLIMETER (INCHES)
2) TOLERANCES:
X.XX ± 0.25 [0.01]

I/O INTERCONNECT SANTA ANA, CALIFORNIA	
DR. BY: JERRY SUN DR. CHECKER:	TITLE: 26 AWG (7/34) BARE COPPER, NON-UL UNSHIELDED, MODULAR CABLE
REV:	DWG NO: GLF-120-X10-0X0
DESIGNER:	PART NO: GLF-120-X10-0X0
CURT/SALES:	CUSTOMER: I/O INTERCONNECT
REV:	SCALE: NONE
SHEET 2 OF 2	