






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	DIMENSIONS									WEIGHT lbs. (grams)
	A	B	C	D	E	F	G	H	J	
CMW-KIT10	2.00 (50.8)	1.00 (25.4)	5.25 (133.4)	9.58 (243.3)	1.75 (44.4)	3.00 (76.2)	1.20 (30.5)	3.33 (84.6)	4.87 (124.5)	.606 (274.9)
CMWB10	—	—	5.24 (133.4)	—	1.75 (44.4)	—	1.20 (30.5)	—	—	.230 (104.3)
CMWW10	2.00 (50.8)	1.00 (25.4)	—	—	—	3.00 (76.2)	—	3.33 (84.6)	4.87 (124.5)	.188 (85.3)

Notes:

- 1* See current price sheet for part number suffix designation for package size and color.
2. Flame retardant cable ties (Qty. 3, PLT25-M60) included with CMWB and CMW-KIT10.



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G002391T_PB_CMW10_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

CABLE MANAGEMENT WATERFALL
(CMW-KIT10, CMWB10, CMWW10)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.03 (0.8) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

1	4/17/03	LGG		CHG DIM C & D FOR CMW-KIT WAS 5.24(133.4) & 9.60(243.3). ADD 'REF' TO DIM 'A'	G802391T	1				DRAWN BY	LGG	MAT'L:	SCALE	1/4
R	8/27/01	LGG		INITIAL RELEASE	G802391T	R				DATE	8/27/01	GLASS REINFORCED FLAME RETARDANT NYLON 6/6	DRAWING NO.	GB02391T
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D			DWG SIZE	A