








- 1
- 2
- 3
- PART ACCEPTS 3.18 [.125] RECEPTACLE CONTACT P/N 1217039-1.
- GLOW WIRE COMPLIANT PER IEC 60335-1 750C NO FLAME.
- PRELIMINARY - NOT FOR PRODUCTION.



NATURAL	2 PA6 V-2	3 521181-3
BLACK	NYLON 66/6 UL94 VO	521181-2
BLACK	NYLON 66	521181-1
COLOR	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
PA6 V-2

2

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
COLOR-NATURAL

DWN
PHILLIP M. FORTNEY
28/JUL/98

CHK
JEFF R. RUTH
28/JUL/98

APVD
DON DECKER
28/JUL/98

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

TE Connectivity

NAME
PLUG,3 CIRCUIT,3.18[.125] BLADE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=521181

RESTRICTED TO
—

SCALE
2:1

SHEET
1 OF 1

REV
F2