

PART
NAME

PLASTIBOX (STYLE B)

PART
No.

PWS-11291



MATERIAL: HIGH-IMPACT ABS
 COLOR: BLACK OR GRAY
 FINISH: TEXTURED BODY WITH
 SMOOTH TOP INSERT

TWO (2) #4 x 0.250" LG. SCREWS AND
 TWO (2) #4 x 0.375 LG. SCREWS
 SUPPLIED FOR ASSEMBLING TOP.


FOUR (4) #4 x 1/2 LG. FLAT HEAD
 SCREWS SUPPLIED FOR WALL MOUNTING.

*-USABLE AREA ON COVER AVAILABLE
 FOR CUSTOM MOLDING.

NOTE: ALL DIMENSIONS HAVE ± 0.015 TOLERANCE
 UNLESS OTHERWISE SPECIFIED.



0.260 DIA. BOSS WITH 0.093 DIA.
 HOLE x 0.156 DEEP (4) PLACES
 MOUNTING BOSSES USE EITHER M2.5 METRIC
 OR #4 STD. SHEET METAL SCREWS
 x 0.188" LG. (NOT SUPPLIED)

PART
NAME

PLASTIBOX (STYLE B)

PART
No.

PBS-11294


MATERIAL: HIGH-IMPACT ABS
 COLOR: BLACK OR GRAY
 FINISH: TEXTURED BODY WITH
 SMOOTH TOP INSERT

TWO (2) #4 x 0.250" LG. SCREWS AND
 TWO (2) #4 x 0.375 LG. SCREWS
 SUPPLIED FOR ASSEMBLING TOP.



FOUR (4) NON-SKID PUSH-ON FEET SUPPLIED

*-USABLE AREA ON COVER ALSO
 AVAILABLE FOR CUSTOM MOLDING.

NOTE: ALL DIMENSIONS HAVE ± 0.015 TOLERANCE
 UNLESS OTHERWISE SPECIFIED.



AREA FOR
 CUSTOM
 MOLDING



0.260 DIA. BOSS WITH 0.093 DIA.
 HOLE x 0.310 DEEP (4) PLACES
 MOUNTING BOSSES USE EITHER M2.5 METRIC
 OR #4 STD. SHEET METAL SCREWS
 x 0.250" LG. (NOT SUPPLIED)