



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™



BIT,NAILEATER 7/8(.875) X 18 (66PT-7/8)

Nail Eater Extreme

Cat No: 66PT-7/8

UPC No: 783310309277

Description

- "Improved cutting edge provides 30% longer life span
- Patented new design for improved cutting and cleaner holes
- Self-feeding screw point draws bit through wood
- Unique patented design cutting angle - smoother starts, reduced cutting loads
- Made of super tough, heat-treated steel
- cuts through nails and provides longer life
- "Shorty" bits - for working in tight places, yet still can go through three abutting 2 x 4s
- See "Bit Extensions" if more length is required
- P.O.P packaged "

Specifications

- Bit Diameter : 7/8 IN (22.200 MM)
- Material : Heat Treated Steel
- Overall Length : 18.000 IN (457.200 MM)
- Shank Diameter : 7/16 IN (11.100 MM)
- Shank Type : Hexagonal
- Sub Brand : Nail Eater
- Twist Length : 15.000 IN (381.000 MM)
- Type : Extreme
- Weight : 1.500 LB (681.000 GM)