



BURNDY Catalog Number
UPC Number
Description
Status

BA14EZ10
 7818100265888
 FL FORK. 16-14, 8-10 ST
 Active

Web Use
 BURNDY Product Line

Dimensional

Length (in) 0.96
 Tongue Type Flanged Fork
 Thickness 0.32
 Pad Width (in) 0.41

General

Product Description Copper Terminal, Flanged Fork
 Tongue, 16-14 AWG, #8-#10 Stud,
 Vinyl Insulated, Tin Plated

Conductor(s)

Copper Solid Size (Range) 16 AWG-14 AWG
 Copper Stranded (Range) 16 AWG-14 AWG

Physical

Type of Plating Tin
 Connector Type Terminal - Fork
 Insulation Type Vinyl
 Plated (Yes or No) Y

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175