

REDINGTON COUNTERS, INC.
P.O. Box 608, 130 Addison Road, Windsor, CT 06095
Toll Free: (860) 688-6205 • Fax: 860/688-1591
E-Mail: Info@RedingtonCounters.com • Website: www.RedingtonCounters.com

Item # D2-1284, Model 128 Electromechanical Totalizer



Model 128 Electromechanical Totalizer

A general purpose, 4 figure electromechanical reset counter perfect for applications where long life, reliability, and accuracy are mandatory. Several mounting alternatives and large, easy-to-read numbers are combined in a rugged housing.

SPECIFICATIONS

Model No.	128
Mounting	D Panel Mount
Display	4 Figures, white on black, 0.19 inch (5mm) high
Display Height	0.19 Inch
Display Height	5 mm
No. of Digits	4
Voltage	115 VAC
Tolerance- Voltage	±177 10%, but not to exceed 10 volts
Power	5 watts (nominal)
Reset Type	Knob
Speed	1000 counts/minute (min. 30ms - on, 30ms - off)
Operating Temperature	-15 to +140 °F
Operating Temperature	-26 to +60 °C
Approvals	UL Recognized, CSA Certified, CE Compliant
Termination	(2) No. 22 AWG 105°C wire leads, 8 inch (203mm) long
Weight	10 oz
Weight	284 gm
Operating Life	Beyond 50 million counts

Stock Availability	No
--------------------	----