



Sample photo

Order symbol: UL PC 100/75 HG
Product nbr: 6411302
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074057013
El. number:
Finland:
Electric No. 8212030129
Denmark:
Electric No. Italy: 7351027U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	80	75	Ingress Protection (EN 60529): IP66/67
inch:		5.1	3.1	3.0	Impact Resistance (EN 62262): IK08
					Electrical insulation: Totally insulated
					Halogen free (DIN/VDE 0472, Part 815): 1
					UV resistance: UL 508
					Flammability Rating: UL 746C 5V
					UL Type:
					Glow Wire Test (IEC 695-2-1) °C: 960
Materials:					Certificates:
Material:		Polycarbonate			Germanischer Lloyd (GL)
Base colour:		RAL 7035 -light grey			Underwriters Laboratories
Cover screws material:		Polyamide			SGS Fimko
Cover colour:		RAL 7035 -light grey			UL Canada
Cover screws colour:		Grey			Gost R
Gasket material:		TPE			
Temperatures:					
Temperature °C (short term):		-40 ... 120 °C			
Temperature °C (continuous):		-40 ... 80 °C			
Temperature °F (short term):		-40 ... 250 °F			
Temperature °F (continuous):		-40 ... 175 °F			

