






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/15/04	MCCORMICK



SPECIFICATIONS:

- UL94V-0 COMPLIANT (CONTACT HOUSING)

MATERIALS

- TOP & BOTTOM SHELL: STEEL – TIN/LEAD FINISH
- CONTACTS: COPPER ALLOY
- CONTACT PLATING: SELECTIVE GOLD PLATING

ELECTRICAL

RATING:

- VOLTAGE: 30 VAC (R.M.S.)

ENVIROMENTAL

- OPERATING TEMPERATURE RANGE: -55°C TO +85°C, UNLESS LIMITED BY CABLE OR OVERMOLD (-40°C TO +60°C STORAGE; +0°C TO +40°C OPERATING).

APPLICATION NOTES

- APPLICABLE CABLE DIAMETER: $\phi .134$ TO $\phi .209$

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
.X $\pm .1$
.XX $\pm .05$
.XXX $\pm .005$
CABLE LENGTH TOLERANCE
<300" $\pm 5\%$ >300" $\pm 2\%$

APPROVALS	DATE
DRAWN BY C.MCCORMICK	04/13/2004
CHECKED BY D.PARHAM	04/13/2004
APPROVED BY R.CARRICK	04/13/2004

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com
CONNECTIVITY
PRODUCTS

45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

PRODUCT DESCRIPTION

USB PLUG - SERIES A w/o HOOD

DRAWING TITLE

OUTLINE DRAWING

SIZE	FSCM NO.	DWG. NO.	REV
A	43321	CNUSB-A-OD1	A
SCALE: 2:1		CAD FILE: CNUSB-A-OD1.SLDDRW	SHEET 1 OF 1