

NOTES: (C)

1. DRAWING TO BE INTERPRETED IN ACCORDANCE WITH THE CURRENT REVISION OF ASME Y14.5M.
2. THIS PART/PRODUCT IS TO BE MANUFACTURED WITH THE APPLICABLE REGULATIONS OF EC DIRECTIVES 2002/95/EC AND 2002/96/EC, RESTRICTION OF THE USE OF HAZARDOUS SUBSTANCES IN ELECTRICAL AND ELECTRONIC EQUIPMENT (RoHS) AND WASTE ELECTRICAL AND ELECTRONIC EQUIPMENT (WEEE).
3. TERMINAL IDENTIFICATION SHOWN FOR REFERENCE ONLY. (SWITCH IS NOT MARKED WITH TERMINAL IDENTIFICATION.)

SWITCH CHARACTERISTICS

ELECTRICAL

ELECTRICAL RATING: SEA LEVEL	
LOAD	28VDC
RESISTIVE	2 AMPS
INDUCTIVE	1 AMPS
DWV	1050 VRMS

LOW LEVEL RATING: 10 MILLIAMPERES AT 30 MILLIVOLTS MAX. D.C. OR PEAK A.C. PER MIL-PRF-8805.

ELECTRICAL ENDURANCE: 150,000 MIN. (COMMERCIAL)

MECHANICAL
MECHANICAL ENDURANCE: 500,000 MIN.

PRETRAVEL: 9.5° MAX.

OVER TRAVEL: 1.5° MIN.

RETURN POINT: 4° MIN.

OPERATING FORCE: .75±.25 LBS.

BUTTON STRENGTH: 10 LBS. MIN. PULL
CONTACT MADE IN THE DIRECTION OF BUTTON TRAVEL.

PHYSICAL

TEMPERATURE RANGE: -55°C TO +85°C
SEAL: WATER RESISTANT PER MIL-STD-810F,
METHOD 506.4, PROCEDURE 3 (Drip).

BUTTON: NYLON, CHOICE OF COLOR
(SEE PART NUMBER CODE)



CASE: GLASS FILLED POLYESTER, BLACK

MARKING

OTTO 21649


T4-TCK33- (SEE PART NUMBER CODE)

DATE CODE (YYWW)



PART NUMBER CODE

T 4 - T C K 3 3 -





SCALE 1:1

T4-TCK33_-

REV	OCN #	DATE	APR
A	020710	01 DEC 03	DGK
B	024196	21 SEP 04	DGK
C	049072	29 MAY 09	RAS

CURRENT RATING
 1. STANDARD
 2. LOW LEVEL
 3. STANDARD WITH
 INTERNAL JUMPER
 4. LOW LEVEL WITH
 INTERNAL JUMPER

BUTTON COLOR
 1. RED
 2. BLACK
 8. GRAY



UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES. TOLERANCES: .XX ±.03 .XXX ±.010 ANGLES ±2° DO NOT SCALE	OTTO CARPENTERSVILLE, ILLINOIS USA	DESCRIPTION T4-T, SWITCH, TACTILE MINI TRIM, 4 WAY, 4-WAY JOG BUTTON
DRWN. JFC CHKD. JFC APPD. RTK WT.	SIZE B FSCM NO 21649 DRAWING NO. T4-TCK33_- REV. C	THIRD ANGLE PROJECTION Scale 2:1 Sheet 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

OTTO:

[T4-TCK3338](#) [T4-TCK3312](#) [T4-TCK3322](#) [T4-TCK3332](#) [T4-TCK3318](#)