

Product Information

5377PJO125P30

EAN 4031582324617

Swivel castor with total lock, tail end of castor, Housing and wheels made from high grade synthetic materials, double ball bearing swivel head.

Wheel centre made of Polypropylene, Tread: TENTEPrene (thermoplastic rubber), grey non-marking, plain bearing, bolt hole

Wheel diameter	125 mm
Width of Tread	30 mm
Centre hole	12 mm
Offset	38 mm
Swivel Interference	201 mm
Overall height	161 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.52 Kg / daN
Dynamic Load capacity	100 Kg / daN
Static Load capacity	200 Kg / daN
Hardness of tread	A 87 Shore

