



Female Disconnects – Nylon Insulated Butted Seam Bullet Style




Product Number†	UPC (054007-)	Wire Range (AWG)	Mating Snap Diameter S	L	Barrel Length	Barrel I.D.	Maximum Insulation Diameter	Terminals per: Case
MNU18-156DFIK	02304	22-18	0.156	1.02	0.25	0.095	0.145	1000
MNU18-180DFIK	02305	22-18	0.180	1.02	0.25	0.095	0.145	1000
MNU14-156DFIK	02282	16-14	0.156	1.02	0.25	0.115	0.170	1000
MNU14-180DFIK	02283	16-14	0.180	1.02	0.25	0.115	0.170	1000




MNU18-156DFI
22-18
MVU18-156DM



MNU18-180DFI
22-18
MVU18-180DM



MNU14-156DFI
16-14
MVU14-156DM



MNU14-180DFI
16-14
MVU14-180DM

Wire Range
Suggested Mate