


PART NO.	MATERIAL	"A" +/- .062 LENGTH	"B" +/- .062 IMPRINT	"C" +/- .062 REPEAT	"E" +/- .062	LABELS PER ROW	PKG. QTY.
S100X075T1D	CLEAR Polyvinylidene Fluoride GMTDI	0.75 (19.1)	0.25 (6.35)	1.00 (25.4)	.125 (3.18)	8	5000
S100X138T1D		1.38 (35.1)	0.50 (12.7)	1.50 (38.1)	.060 (1.52)	8	5000
S100X150T1D		1.50 (38.1)	0.50 (12.7)	2.00 (50.8)	0.25 (6.35)	8	5000
S100X244T1D		2.44 (62.0)	0.75 (19.1)	2.50 (63.5)	.030 (.762)	8	1000
S100X387T1D		3.87 (98.3)	1.00 (25.4)	4.00 (101.6)	.065 (1.65)	8	1000
S100X400T1D		4.00 (101.6)	1.00 (25.4)	4.50 (114.3)	0.25 (6.35)	8	1000

NOTES:
1. ALL LABELS TO BE EQUALLY
SPACED AS SHOWN.
2. MILLIMETERS ARE IN [].



										CAD FILENAME/LAYERS				I006I9RS-DS-CI0853/00A			
										PANDUIT CORP. TINLEY PARK, ILLINOIS							
										CUSTOMER DRAWING PVDF SELF-LAM. PRINTABLE LABEL S100X***TID							
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
										DRAWN BY RVU		MAT'L: SEE TABLE			SCALE NTS		
0	9/29/10	RVU		RELEASE TO PRODUCTION.			6160	R			DATE 09/29/10				DRAWING NO. CI0853		DWG A
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP		CHK'D		SIZE		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[S100X150T1D](#) [S100X400T1D](#) [S100X244T1D](#)