


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15015-0851](#)
Status: **Active**
Overview: [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Description: 0.30mm Pitch Premo-Flex™ Etched Copper Polyimide Jumper, Same Side Contacts (Type A), 0.203m Cable Length, 0.12mm Cable Thickness, 51 Circuits

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-15015-001 \(PDF\)](#)

General	
Product Family	Cable
Series	15015
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ FFC and Etched Polyimide Jumpers
Product Name	Premo-Flex™ Jumper
UPC	884982822757
Physical	
Cable Length	0.203m
Circuits (Loaded)	51
Circuits (maximum)	51
Net Weight	1.000/g
Packaging Type	Bag
Pitch - Termination Interface	0.30mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable
Electrical	
Current - Maximum per Contact	0.2A
Voltage - Maximum	50V AC/DC
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-15015-001
Sales Drawing	SD-15015-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS


Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[15015Series](#)

Use With
[502598](#) 0.30mm Pitch Easy-On™
BackFlip™ Type FPC Connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15015-0851