

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [82-26-6820](#)
Status: **Active**
Description: 1.27mm Pitch Round Conductor Flat Cable - 26 AWG (7 x 34) Stranded Tinned, 20 Circuits, Reel 30.48m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR61126
UL E61522

General

Product Family Cable
Series [8863](#)
Crimp Quality Equipment Yes
Geographic Area Asia
Product Name Ribbon
UPC 800754377546

Physical

Cable Length 30.48m
Circuits (Loaded) 20
Insulation PVC
Net Weight 1901.520/g
Packaging Type Reel
Pitch - Termination Interface 1.27mm
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 26
Wire/Cable Type (7x34) Stranded, Tinned

Electrical

Current - Maximum per Contact N/A
Voltage - Maximum 300V

Solder Process Data

Max. Cycles at Max. Process Temperature 0

Material Info

Old Part Number 8863-20-100B

Reference - Drawing Numbers

Sales Drawing SD-8863-001




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[8863Series](#)

Use With

[70121](#) MX-50™ Slimline Ribbon Cable.
[90584](#) Picoflex® PF-50 IDT Receptacle