

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

15166-0441

Status:

Active

Overview:

Premo-Flex™ FFC and Etched Polyimide Jumpers

Description:

0.50mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 40 Circuits, 0.229m Cable Length, Cable Thickness 0.12mm, Tin (Sn) Plating

Documents:

Drawing (PDF)

Product Specification PS-15166-001 (PDF)

Packaging Specification PK-15166-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Cable

Series

15166

Comments

Contacts on the same side, Type A

Crimp Quality Equipment

Yes

Overview

Premo-Flex™ FFC and Etched Polyimide Jumpers

Product Name

Premo-Flex™ FFC Jumper

UPC

884982849396

Physical

Cable Length

0.229m

Circuits (Loaded)

40

Circuits (maximum)

40

Net Weight

1.000/g

Packaging Type

Bag

Pitch - Termination Interface

0.50mm

Temperature Range - Operating

-40°C to +105°C

Wire Size AWG

N/A

Wire/Cable Type

Flat Flex Cable

Electrical

Current - Maximum per Contact

0.5A

Voltage - Maximum

60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification

PK-15166-001

Product Specification

PS-15166-001

Sales Drawing

SD-15166-001



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

15166Series

Use With

Molex FFC – FPC connector.
Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION