


SPECIFICATIONS		
PARAMETERS	VALUES	UNITS
RATED VOLTAGE	10	Vp-p
OPERATING VOLTAGE RANGE	1 ~ 30	Vp-p
RATED CURRENT (MAX)	5	mA
CAPACITANCE	15,000 ± 30%	pF
MINIMUM SPL @ 10 CM	80	dBa
RESONANT FREQUENCY	4,800 ± 500	Hz
OPERATING TEMPERATURE	-20 ~ +70	°C
STORAGE TEMPERATURE	-30 ~ +75	°C
HOUSING MATERIAL	ABS	-
TERMINAL MATERIAL	LEAD WIRES	-
WEIGHT	1	grams

©2003, Projects Unlimited Inc.

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	6/14/2006	
A	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	4/10/2008	B.R.



1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-1348-TF-LW90-R](#)