

main menue



- home
- test & measurement
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
 - ▶ 0,64 mm system
 - ▶ 2 mm system
 - ▶ 2 mm Sicherheitssystem
 - ▶ 4 mm system
 - ▶ 4 mm sliding sleeve system
 - ▶ 4 mm safety system
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
- sets
- miscellaneous

company

- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

Home ▶ clamp-type test probes ▶ clamp-type test probe ▶ KLEPS 2 BU


KLEPS 2 BU

datasheet for KLEPS 2 BU
article number: 973501101



[View Full-Size Image](#)



product description:		order number: 973 501-101
description:		Miniature clamp-type test probe with 2 mm diameter socket connection. Gold-plated copper beryllium contact spring. Gold-plated sprung bronze contact hook for wires up to a maximum diameter of 2 mm. Suitable for connection to wrap posts up to a maximum of
typ:		KLEPS 2 BU rot / red
system:		2mm system
order number:		973 501-101
clamping range:		max. Ø 2 mm
clamping typ:		contact hook
color		
other color versions:		 
technical data		
measurement category acc. to IEC 61010:		CAT I
type of termination:		2 mm socket (spring-loaded)
rated voltage:		30 VAC / 60 VDC
rated current:		6 A
Please consider derating curve!		
contact resistance:		10 mOhm
material		
contact material:		contact hook: bronze contact spring: copper - beryllium
contact surface material:		gold
housing material:		PA
environmental conditions:		
temperature range:		-25 °C to +100 °C
inflammable class:		
housing (basic material):		UL 94 V - 2
drawing		
		

search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code

