










LOC	DIST	REVISIONS						
AI	-	ÄNDERUNGEN						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
		BESCHREIBUNG						
PROJEKT NR.:								
-			D3	ECR-15-004594	26MAR15	RK		MKO




NOTES:


- 1 SUITABLE CRIMP CONTACTS: SERIES HE/HA
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM
- 2 SUITABLE HOOD SIZE 5; 7; 9; 11: SERIES HA; HD
SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 0,5x3 DIN 5264
- 3 Strip lenght: Screw conection 10mm
Spring clamp conection 10mm Crimp conection 7.5mm
- 4 STANDARDS:
DIN EN 61984; DIN EN 60664-1

5. PACKAGING:
5 SETS IN A CARTON, PRE-MOUNTED
6. SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 300 PIECES
7. SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 150 PIECES
8. SPECIAL PACKAGING: AIS
PACKAGING UNIT: 250 PIECES
9. SPECIAL PACKAGING: WIELAND
PACKAGING UNIT: 100 PIECES

Panel cut-out for contact insert when used without housing



Assembling instruction



 DISTANCE FOR SAFETY
CONTACT MARKING MAX. 24 mm

[illegible]