


# EUREKA Series

## CONNECTORS


Rated operating voltage > 50 V

Reference standards: EN 60309-1 and EN 60309-2

## STRAIGHT



IP44



IP66/67

| Poles  | Hz       | Volt        | Colour | Inlet<br>Pack Quantity:<br>h |                                |                               |                                            |                              |
|--------|----------|-------------|--------|------------------------------|--------------------------------|-------------------------------|--------------------------------------------|------------------------------|
|        |          |             |        |                              | 16 A<br>cable sleeve<br>10/100 | 32 A<br>cable sleeve<br>10/50 | 16 A<br>cable gland<br>10/100 <sup>1</sup> | 32 A<br>cable gland<br>10/40 |
| 2P+E   | 50/60    | 100-130     |        | 4                            | 311.1640<br>311.1640G *        | 311.3240<br>311.3240G *       | 316.1640                                   | 316.3240                     |
|        | 50/60    | 200-250     |        | 6                            | 311.1643<br>311.1643G *        | 311.3243<br>311.3243G *       | 316.1643                                   | 316.3243                     |
|        | 50/60    | 380-415     |        | 9                            | 311.1648                       | 311.3248                      | 316.1648                                   | 316.3248                     |
|        | 60       | 277         |        | 5                            | 311.16437                      | 311.32437                     | 316.16437                                  | 316.32437                    |
|        | 50/60    | 480-500     |        | 7                            | 311.16436                      | 311.32436                     | 316.16436                                  | 316.32436                    |
|        | 50/60    | is. transf. |        | 12                           | 311.16433                      | 311.32433                     | 316.16433                                  | 316.32433                    |
|        | >300-500 | >50         |        | 2                            | 311.16432                      | 311.32432                     | 316.16432                                  | 316.32432                    |
|        | d.c.     | >50-250     |        | 3                            | 311.16434                      | 311.32434                     | 316.16434                                  | 316.32434                    |
|        | d.c.     | >250        |        | 8                            | 311.16438                      | 311.32438                     | 316.16438                                  | 316.32438                    |
| 3P+E   | 50/60    | 100-130     |        | 4                            | 311.1641                       | 311.3241                      | 316.1641                                   | 316.3241                     |
|        | 50/60    | 200-250     |        | 9                            | 311.1644                       | 311.3244                      | 316.1644                                   | 316.3244                     |
|        | 50/60    | 380-415     |        | 6                            | 311.1646<br>311.1646G *        | 311.3246<br>311.3246G *       | 316.1646                                   | 316.3246                     |
|        | 60       | 440-460     |        | 11                           | 311.16465                      | 311.32465                     | 316.16465                                  | 316.32465                    |
|        | 50/60    | 480-500     |        | 7                            | 311.16466                      | 311.32466                     | 316.16466                                  | 316.32466                    |
|        | 50/60    | 600-690     |        | 5                            | 311.16467                      | 311.32467                     | 316.16467                                  | 316.32467                    |
|        | 50/60    | is. transf. |        | 12                           | 311.16463                      | 311.32463                     | 316.16463                                  | 316.32463                    |
|        | 50<br>60 | 380<br>440  |        | 3                            | 311.16464                      | 311.32464                     | 316.16464                                  | 316.32464                    |
|        | 100-300  | >50         |        | 10                           | 311.16461                      | 311.32461                     | 316.16461                                  | 316.32461                    |
|        | >300-500 | >50         |        | 2                            | 311.16462                      | 311.32462                     | 316.16462                                  | 316.32462                    |
| 3P+N+E | 50/60    | 100-130     |        | 4                            | 311.1642                       | 311.3242                      | 316.1642                                   | 316.3242                     |
|        | 50/60    | 208-250     |        | 9                            | 311.1645                       | 311.3245                      | 316.1645                                   | 316.3245                     |
|        | 50/60    | 346-415     |        | 6                            | 311.1647<br>311.1647G *        | 311.3247<br>311.3247G *       | 316.1647                                   | 316.3247                     |
|        | 50/60    | 480-500     |        | 7                            | 311.16476                      | 311.32476                     | 316.16476                                  | 316.32476                    |
|        | 50/60    | 600-690     |        | 5                            | 311.16477                      | 311.32477                     | 316.16477                                  | 316.32477                    |
|        | 60       | 440-460     |        | 11                           | 311.16475                      | 311.32475                     | 316.16475                                  | 316.32475                    |
|        | 50<br>60 | 380<br>440  |        | 3                            | 311.16474                      | 311.32474                     | 316.16474                                  | 316.32474                    |
|        | >300-500 | >50         |        | 2                            | 311.16472                      | 311.32472                     | 316.16472                                  | 316.32472                    |

\*Glanded version

<sup>1</sup>3P+N+E=Pack Qty. 10/40