Pin Header SMD Shrouded 1,25 mm

Series **427**



Rated current	1,0 A
Rated voltage	100 VRMS / VDC
Withstand voltage	300 VRMS for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

pitch **1,25**

termination

max. pincount **015**

Product group **3**

Variation

1



2



PCB Layout





no. of contacts	see figure left	see figure left	available in variation	
n	A	B		
002	7,25	4,25	1	2
003	8,50	5,50	1	2
004	9,75	6,75	1	2
005	11,00	8,00	1	2
006	12,25	9,25	1	2
007	13,50	10,50	1	2
008	14,75	11,75	1	2
009	16,00	13,00	1	2
010	17,25	14,25	1	2
011	18,50	15,50	1	2
012	19,75	16,75	1	2
013	21,00	18,00	1	2
014	22,25	19,25	1	2
015	23,50	20,50	1	2

Plating:
T = Sn

Packaging:
S = Standard
R = Reel

Variation (1,2) | No. of contacts | Plating contact | Packaging (S,R)

GARRY

www.mpe-connector.de

CS060212_V2

Order code: 427-?-???-0-T-K?0

Mating series	425
see page	6-3

MPE-Garry GmbH • Schäfflerstraße 13 • 87629 Füssen • Germany • Phone: +49 (0) 83 62 / 91 56-0 • Fax: +49 (0) 83 62 / 91 56-500 • Email: vk@mpe-connector.de • www.mpe-connector.de