



INTERVOX

? [Product Overview](#)

[Advanced Product Search](#)

Search By Part #:

GO

Quick Pick Search

- ? [Transducers](#)
- ? [AC Buzzers](#)
- ? [Surface mounts](#)
- ? [Piezo Electrics](#)
- ? [Piezo Elements](#)
- ? [Electronic Buzzers](#)
- ? [Speakers](#)
- ? [Microphones](#)
- ? [Catalog Request](#)

[SEARCH
DISTRIBUTOR
INVENTORY](#)

INTERCAP


? [Product Overview](#)

? [Catalog Request](#)

[Home](#) · [Company Profile](#) · [Sales](#) · [Tracking Center](#) · [What's New](#) · [Contact Us](#)

[Previous Page](#)

AC PIEZO BUZZER



ROHS COMPLIANT

PART NUMBER:
BRP4549S240-C

Search Distributor Inventory For This Part: If "No parts were found", please contact us at 800-645-9154 or your local distributor.

SPECIFICATIONS:

RATED VOLTAGE:	240 AC
OPERATING VOLTAGE:	60 ~ 250 AC
MAX CURRENT:	20 mA
SOUND OUTPUT LEVEL:	90dB @ 30 cm
TERMINAL TYPE:	2 SCREW LUGS
RESONANT FREQUENCY:	2900 ± 500 Hz
OPERATING TEMPERATURE:	-20 TO +60 °C
TONE MODE:	CONTINUOUS
FRAME DIAMETER:	43.5 mm
FRAME DEPTH:	49.5 mm
MOUNTING DIMENSIONS:	Panel Mount

DIMENSIONS:

